

Datasheet for #sbcw1241 DN

Recommendations:

Please read the starter kit user manual (at least installation chapter 5), if available, and have a look at the FAQ at <http://www.alpeslasers.ch/alfaq.pdf>

WARNING: Operating the laser with higher current or voltage than specified in this document may cause damage and will result in loss of warranty, unless Alpes Lasers has permitted to do so!

WARNING: Beware of the polarity of the laser. This laser has to be powered with negative current on the laser contact (= bonding pad, corresponding to the label "laser" on the LLH) and the positive current on the base contact (= submount, corresponding to the label "base" on the LLH). To use with a power-supply ILX Lightwave LDX-3232 or equivalent.




Figure 1: Support mounting for #sbcw1241 DN (please note that the laser is connected to the DN pad drawn in blue)




Figure 2: Output power as a function of the singlemode emission frequencies and temperatures




Figure 3: Applied DC current as a function of singlemode emission frequencies and temperatures

λ [nm]	ν [cm ⁻¹]	P[mW]	Temp[°C]	U_{LASER} [V]	I[A]
4519.2	2212.8	0.1	-153	8.7	0.28
4520.4	2212.2	4.7	-153	8.8	0.32
4522.1	2211.4	0.1	-143	8.6	0.29
4524	2210.4	7.3	-143	8.7	0.35
4525.9	2209.5	17.2	-143	8.9	0.41
4525.6	2209.7	0.1	-133	8.6	0.31
4527.5	2208.7	7.2	-133	8.7	0.37
4529.5	2207.8	15.4	-133	8.8	0.43
4530.8	2207.1	19.8	-133	8.9	0.47
4529.6	2207.7	0.1	-123	8.5	0.34
4531.3	2206.9	3.7	-123	8.6	0.39
4532.9	2206.1	9.3	-123	8.7	0.44
4535.1	2205	14.9	-123	8.8	0.5
4534.2	2205.4	0.1	-113	8.5	0.39
4536.2	2204.5	3.8	-113	8.6	0.44
4538.4	2203.4	8.6	-113	8.7	0.5
4539.9	2202.7	0.1	-103	8.5	0.46
4541.6	2201.8	2	-103	8.6	0.5

Table 1 : singlemode optical output power as function of operating parameters




Figure 4: voltage and avg power vs current in continuous-wave operation (the solid squares indicate the maximum singlemode emitted power)





Figure 5: voltage and avg power vs current in continuous-wave operation (including the multimode region)

Note: at 120K: $I_{th}=280\text{mA}$ / $V_{th}= 8.7\text{V}$ (2-wires measurements). Maximum operation current: 0.5A for all temperatures.

Figure 4: spectra at different temperatures for various DC currents






Figure 6: spectra at 120K




Figure 7: spectra at 120K (monomode range)




Figure 8: spectra at 130K




Figure 9: spectra at 130K (monomode range)




Figure 10: spectra at 140K




Figure 11: spectra at 140K (monomode range)

Figure 11: spectra at 150K, 160K and 170K (all monomode)

