

**Datasheet for #sbcw1875 DN**

Recommendations:

Please read the starter kit user manual (at least installation chapter 5), if available, and have a look at the FAQ at <http://www.alpeslasers.ch/alfaq.pdf>

**WARNING:** Operating the laser with higher current or voltage than specified in this document may cause damage and will result in loss of warranty, unless Alpes Lasers has permitted to do so!

**WARNING:** Beware of the polarity of the laser. This laser has to be powered with negative current on the laser contact (= bonding pad, corresponding to the label "laser" on the LLH) and the positive current on the base contact (= submount, corresponding to the label "base" on the LLH). To use with a power-supply ILX Lightwave LDX-3232 or equivalent.



Figure 1: Support mounting for #sbcw1875 DN (please note that the laser is connected to the DN pad drawn in blue)




Figure 2: Output power as a function of the singlemode emission frequencies and temperatures




Figure 3: Applied DC current as a function of singlemode emission frequencies and temperatures

$\lambda$ [nm]	$\nu$ [cm <sup>-1</sup> ]	P[mW]	Temp[°C]	$U_{LASER}$ [V]	I[A]
9097.1	1099.3	0.1	-193	11.1	0.71
9099.1	1099	0.6	-193	11.1	0.73
9117.5	1096.8	1.3	-193	11.2	0.76
9125.4	1095.8	18.2	-193	11.4	0.86
9134.3	1094.8	27.4	-193	11.6	0.96
9123.3	1096.1	0.1	-183	10.9	0.75
9131.5	1095.1	14.4	-183	11.1	0.85
9142.4	1093.8	22.4	-183	11.4	0.96
9132.8	1094.9	0.1	-173	10.8	0.77
9136.9	1094.5	5.7	-173	10.9	0.82
9140.3	1094.1	10.5	-173	11	0.86
9145.1	1093.5	14.1	-173	11.1	0.91
9150.3	1092.9	15	-173	11.3	0.96
9141.3	1093.9	0.1	-163	10.7	0.79
9145.5	1093.4	2.3	-163	10.8	0.84
9150.5	1092.8	5.3	-163	11	0.89

Table 1 : singlemode optical output power as function of operating parameters





Figure 4: voltage and avg power vs current in continuous-wave operation (the solid squares indicate the maximum singlemode emitted power)

Note: at 80K:  $I_{th}$ =710mA /  $V_{th}$ = 11.1V (2-wires measurements). Maximum operation current: 0.96A for all temperatures.

Figure 3: spectra at different temperatures for various DC currents






Figure 5: spectra at 80K for various DC currents (mode jumping for  $I > 0.73A$ , same mode as at higher temperature, see Fig. 1)




Figure 6: spectra at 90K, 100K and 110K for various DC currents (all monomode on the same mode, see Fig. 1)